

WAD33629, WEJTAP Applied In-Line Disconnect Switch

By Burndy
Catalog # [WAD33629](#)

MAX RANGE: .642 - .723 ACSR: 266.8 (26/7), 336.4 (18/1), (26/7)
AAC: 336, 350, 397.5, 477 COMPACT 29 kV, 150 BIL.



General

Catalog Number	WAD33629
Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810462140
UPC 12 Digit	7818104621400

Dimensions

Dimension - B Length fraction	17-9/10 in
Dimension - B Length inch	17.9 in
Dimension - Length Overall inch	48 in

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 5005 Size Range	312.8 (19) kcmil-394.5 (19) kcmil
Conductor - AAAC 6201 Size	312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 6201 Size Range	312.8 (19) kcmil-394.5 (19) kcmil
Conductor - ACSR Str Size	266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil

Conductor - ACSR Str Size Range	266.8 (26/7) Owl kcmil-336.4 (30/7) Oriole kcmil
Conductor - AL Str Size	336 kcmil;350 kcmil;397 kcmil
Conductor - AL Str Size Range	336 kcmil-397 kcmil
Conductor Type	<ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - WAD33629_MODEL-IGES](#)
- [3D Models - WAD33629_MODEL-PDF](#)
- [3D Models - WAD33629_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10083326](#)
- [Specifications - WAD33629](#)