



WCY52PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # WCY52PB



Wejtap connector installed with Yellow booster, .537-.750 Run, .364-.588 (Tap).

General

Catalog Number	WCY52PB
Color	Yellow
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810870464
UPC 12 Digit	7818108704644

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.37 in

Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penguin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin-397.5 (26/7) Ibis
Conductor - ACSR Str Tap	1 (6/1) Robin;1/0 (6/1) Raven;2/0 (6/1) Quail;3/0 (6/1) Pigeon;4/0

(6/1) Penguin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing	
Conductor - ACSR Str Tap Range	1 (6/1) Robin-266.8 (18/1) Waxwing
Conductor - AL Str Run	4/0;250;266.8;300;336.4;350;397.5
Conductor - AL Str Run Range	4/0-450
Conductor - AL Str Tap	1;1/0;2/0;3/0;4/0;250;266.8
Conductor - AL Str Tap Range	1-266.8
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	NC
Status	

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WEJTAP_POWER_LUG_LineArt](#)
- [Sales Drawings - 50014998](#)
- [SDS - WEJTAP Power Booster SDS](#)
- [Specifications - WCY52PB](#)

