



WCY55, WEJTAP Connector

By Burndy
Catalog # WCY55



Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.370 (Max), 1.140 (Min).

Application

For use in tap applications using large run and tap conductor sizes

General

| | |
|-------------------|------------------|
| Connector Type | Tap |
| EU RoHS Indicator | Yes |
| Material | Aluminum |
| Sub Brand | WEJTAP |
| Trade Name | WEJTAP™ |
| Type | Wejtap Connector |
| UPC | 781810874158 |
| UPC 12 Digit | 7818108741588 |

Dimensions

| | |
|---|---------|
| Dimension - F Width Center to Center inch | 3 in |
| Dimension - G inch | 1.37 in |

Conductor Related

| | |
|--------------------------------|--|
| Conductor - ACSR Str Run | 4/0 (6/1) Penquin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis |
| Conductor - ACSR Str Run Range | 4/0 (6/1) Penquin-397.5 (26/7) Ibis |
| Conductor - ACSR Str Tap | 2/0 (6/1) Quail;3/0 (6/1) Pigeon;4/0 (6/1) Penquin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet |
| Conductor - ACSR Str Tap Range | 2/0 (6/1) Quail-336.4 (26/7) Linnet |
| Conductor - AL Str Run | 4/0;250;266.8;300;336.4;350;397.5;400;450 |
| Conductor - AL Str Run Range | 4/0-450 |
| Conductor - AL Str Tap | 3/0;4/0;250;266.8;300;336.4;350;397.5 |
| Conductor - AL Str Tap Range | 3/0-397.5 |
| Conductor Type | <ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap |

Certifications And Compliance

Certification - CSA Approved - No

Certification - CSA Approved No
Standards - RoHS Compliance CM
Status

Logistics

Minimum Pack Quantity 10

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)
[Sales Drawings - 50008861](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-WCY55-SPEC-EN | REV 5/2024