

WCY60PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # WCY60PB



Wejtap Assembly, 450 kcmil-700 kcmil (Run), 450 kcmil-700 kcmil (Tap), Wiring taps.

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCY60PB
Color	Yellow
Connector Type	Tap
EU RoHS Indicator	No
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector with Booster
UPC	781810870549
UPC 12 Digit	7818108705499

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

Conductor Related

Conductor - ACSR Str Run	336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run Range	336.4 (26/7) Linnet kcmil-556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Tap	336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur

Conductor - ACSR Str Tap Range	kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil 336.4 (26/7) Linnet kcmil-556.5 (30/7) Eagle kcmil
Conductor - AL Str Run	450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil
Conductor - AL Str Run Range	450 kcmil-700 kcmil
Conductor - AL Str Tap	450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil
Conductor - AL Str Tap Range	450 kcmil-700 kcmil
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	NC

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_WEJTAP_POWER_LUG_LineArt](#)
[Sales Drawings - 50014998](#)
[SDS - WEJTAP Power Booster SDS](#)
[Specifications - WCY60PB](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-WCY60PB-SPEC-EN | REV 10/2024