

WCB20, WEJTAP Connector

By Burndy
Catalog # [WCB20](#)



Wejtap Assembly , Installed With Blue Booster,Run:.568-.364,
Tap:.572-.386.

Features

WEJTAP Connector installed with Blue Power Booster

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCB20
Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810872956
UPC 12 Digit	7818108729566

Dimensions

Dimension - F Width Center to Center inch	1.64 in
Dimension - G inch	1.04 in

Conductor Related

Conductor - ACSR Str Run	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Run Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG

Conductor - ACSR Str Tap	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG
Conductor - AL Str Run	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Tap Range	2/0 AWG-4/0 AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WCB_Lineart](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCB20](#)