



# WCY82PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # WCY82PB



WEJTAP Connector, 1.133 - 0.889 (Run), 0.436 - 0.324 (Tap), With Yellow Power Booster Assembly.

### General

|                |               |
|----------------|---------------|
| Catalog Number | WCY82PB       |
| Color          | Yellow        |
| Connector Type | Tap           |
| Material       | Aluminum      |
| Trade Name     | WEJTAP™       |
| UPC            | 781810870761  |
| UPC 12 Digit   | 7818108707611 |

### Dimensions

|   |         |
|---|---------|
| Dimension - F Width Center to Center inch | 3.5 in  |
| Dimension - G inch                        | 1.79 in |

### Conductor Related

|                                |   |
|--------------------------------|---|
| Conductor - ACSR Str Run       | 477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard |
| Conductor - ACSR Str Run Range | 477.0 (30/7) Hen-795 (30/19) Mallard  |
| Conductor - ACSR Str Tap       | 2 (6/1) Sparrow;2 (7/1) Sparate;1 (6/1) Robin;1/0 (6/1) Raven;2/0 (6/1) Quail   |

|                                |  |
|--------------------------------|--|
| Conductor - ACSR Str Tap Range | 2 (6/1) Sparrow-2/0 (6/1) Quail  |
| Conductor - AL Str Run         | 556.5;600;636;650;700;715.5;750;795.5;556.5-1000   |
| Conductor - AL Str Run Range   | 556.5-1000   |
| Conductor - AL Str Tap         | 2;1/0;2/0;3/0  |
| Conductor - AL Str Tap Range   | 2-3/0  |
| Conductor Type                 | <ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul> |

### Certifications And Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | NC |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_WEJTAP\\_POWER\\_LUG\\_LineArt](#)
- [Sales Drawings - 50014998](#)
- [SDS - WEJTAP Power Booster SDS](#)
- [Specifications - WCY82PB](#)