

# WCB24, WEJTAP Connector

By Burndy  
Catalog # [WCB24](#)



Wejtap connector installed with blue booster, .532-.650 (Run), .324-.500 (Tap).

## Application

For use in tap applications using large run and tap conductor sizes

## General

Catalog Number	WCB24
Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810873151
UPC 12 Digit	7818108731511

## Dimensions

Dimension - F Width Center to Center inch	1.89 in
Dimension - G inch	1.05 in

## Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penquin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
--------------------------	---

Conductor - ACSR Str Run Range	4/0 (6/1) Penquin AWG-266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Tap	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	1 (6/1) Robin AWG-1/0 (6/1) Raven AWG
Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Run Range	250 kcmil-300 kcmil
Conductor - AL Str Tap	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Tap Range	1 AWG-3/0 AWG

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	25
-----------------------	----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_WCB\\_Lineart](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCB24](#)