

WCB47, WEJTAP Connector

By Burndy
Catalog # [WCB47](#)



Wejtap Assembly , Installed With Blue Booster,Run:.684-.600,
Tap:.684-.600.

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCB47
Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810873755
UPC 12 Digit	7818108737555

Dimensions

Dimension - F Width Center to Center inch	2 in
Dimension - G inch	1.1 in

Conductor Related

Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil- 336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge

Conductor - ACSR Str Tap Range	kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil 266.8 (18/1) Waxwing kcmil- 336.4 (18/1) Merlin kcmil
Conductor - AL Str Run	300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Tap	300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Tap Range	300 kcmil-350 kcmil

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WCB_Lineart](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCB47](#)