

# WCY106PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY106PB](#)



Conn ANSI CL:AA RUS.

## General

Catalog Number	WCY106PB
Color	Yellow
Connector Type	Tap
Material	Aluminum
UPC	781810137833
UPC 12 Digit	7818101378333

## Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	2.04 in

## Conductor Related

Conductor - ACSR Str Run	1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Run Range	1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Tap	636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil;715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil
Conductor - ACSR Str Tap Range	636 (30/19) Egret kcmil-795 (30/19) Mallard kcmil

Conductor - AL Str Run	1100 kcmil;1113 kcmil;1192 kcmil;1200 kcmil;1250 kcmil;1272 kcmil;1300 kcmil
Conductor - AL Str Run Range	1100 kcmil-1300 kcmil
Conductor - AL Str Tap	750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil
Conductor - AL Str Tap Range	750 kcmil-900 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_WEJTAP\\_POWER\\_LUG\\_LineArt](#)
- [Sales Drawings - 50014998](#)
- [Specifications - WCY106PB](#)