

WCY111PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # WCY111PB



CONN ANSI CL:AA RUS.

General

Catalog Number	WCY111PB
Color	Yellow
Connector Type	Tap
Material	Aluminum
UPC	781810246030
UPC 12 Digit	7818102460300

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	2.04 in

Conductor Related

Conductor - ACSR Str Run	1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Run Range	1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Tap	336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil
Conductor - ACSR Str Tap Range	336.4 (18/1) Merlin kcmil-397.5 (30/7) Larkspur kcmil
Conductor - AL Str Run	1100 kcmil;1113 kcmil;1192 kcmil;1200 kcmil;1250

Conductor - AL Str Run Range	kcmil;1272 kcmil;1300 kcmil
Conductor - AL Str Tap	1100 kcmil-1300 kcmil
Conductor - AL Str Tap Range	350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WEJTAP_POWER_LUG_LineArt](#)
- [Sales Drawings - 50014998](#)
- [Specifications - WCY111PB](#)