

WCY82, WEJTAP Connector

By Burndy
Catalog # [WCY82](#)



WEJTAP Connector, 1.133 - 0.889 (Run), 0.436 - 0.324 (Tap), Installed With Yellow Booster.

General

Catalog Number	WCY82
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810875506
UPC 12 Digit	7818108755066

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.79 in

Conductor Related

Conductor - ACSR Str Run	477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Tap	2 (6/1) Sparrow;2 (7/1) Sparate;1 (6/1) Robin;1/0 (6/1) Raven;2/0 (6/1) Quail
Conductor - ACSR Str Tap Range	2 (6/1) Sparrow-2/0 (6/1) Quail

Conductor - AL Str Run	556.5;600;636;650;700;715.5;750;795.5;
Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Tap	2;1/0;2/0;3/0
Conductor - AL Str Tap Range	2-3/0
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)
[Sales Drawings - 50008861](#)
[Specifications - WCY82](#)