

WCY84, WEJTAP Connector

By Burndy
Catalog # WCY84



Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.369 (Max), 1.221 (Min).

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCY84
Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810875605
UPC 12 Digit	7818108756055

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.79 in

Conductor Related

Conductor - ACSR Str Run	477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Tap	6 (6/1) Turkey;5 (6/1) Thrush;4 (6/1) Swan;4 (7/1) Swanate;3 (6/1) Swallow;2

Conductor - ACSR Str Tap Range	(6/1) Sparrow;2 (7/1) Sparate;1 (6/1) Robin
Conductor - AL Str Run	6 (6/1) Turkey-1 (6/1) Robin
Conductor - AL Str Run Range	556.5;600;636;650;700;715.5;750;795.5;556.5-1000
Conductor - AL Str Tap	6;4;3;2;1;1/0
Conductor - AL Str Tap Range	6-1/0
Conductor Type	<ul style="list-style-type: none"> ACSR C Str-Run AL C Str-Run ACSR C Str-Tap AL C Str-Tap

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCY84](#)