



WCY84PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # WCY84PB



Wejtap connector installed with Yellow booster, .889-.1133 Run, .203-.333 (Tap).

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCY84PB
Color	Yellow
Connector Type	Tap
EU RoHS Indicator	No
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector with Booster
UPC	781810870785
UPC 12 Digit	7818108707855

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.79 in

Conductor Related

Conductor - ACSR Str Run	477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard

Conductor - ACSR Str Tap	6 (6/1) Turkey;5 (6/1) Thrush;4 (6/1) Swan;4 (7/1) Swanate;3 (6/1) Swallow;2 (6/1) Sparrow;2 (7/1) Sparate;1 (6/1) Robin
Conductor - ACSR Str Tap Range	6 (6/1) Turkey-1 (6/1) Robin
Conductor - AL Str Run	556.5;600;636;650;700;715.5;750;795.5;
Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Tap	6;4;3;2;1;1/0
Conductor - AL Str Tap Range	6-1/0
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WEJTAP_POWER_LUG_LineArt](#)
- [Sales Drawings - 50014998](#)
- [SDS - WEJTAP Power Booster SDS](#)
- [Specifications - WCY84PB](#)

