


# YA2CDTS, Compression Terminal, #2 AWG, 1-Hole, Long Barrel, Soldered Seam



By Burndy  
Catalog # [YA2CDTS](#)

HYDENT.

## Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

## Application

Wire Termination

## General

Catalog Number	YA2CDTS
Color Code	Brown
Connector Type	LONG BARREL
Die Index	10
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810090459
UPC 12 Digit	7818100904599

## Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - D inch	0.59 in
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	56 mm

Dimension - Length Overall inch	2.22 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.59 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	5/16
Dimension - Z (inch)	0.21 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes


## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	46400

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - SD079849-03](#)  
[Specifications - YA2CDTS](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



©2024 Hubbell Incorporated. All rights reserved  
BRDY-YA2CDTS-SPEC-EN | REV 10/2024