

YA454N, Compression Terminal, 1250 kcmil Cu, 4-Hole, 1/2" Stud, 1- 3/4" Spacing, Long Barrel

By Burndy
Catalog # [YA454N](#)



Copper Compression Lug, 4 Hole w/o Inspection Window, 1250 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel, Tin Plated.

Application

Wire Termination

General

Catalog Number	YA454N
Color Code	Yellow
Connector Type	LONG BARREL
Die Index	29
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	4
Physical Attribute - Tongue Type	straight
Plated	Y
Plating Type	Tin plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810035665
UPC 12 Digit	7818100356655

Dimensions

Dimension - B Length inch	3.19 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	189 mm
Dimension - Length Overall inch	7.44 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.69 in

Dimension - Pad Width inch	3 in
Dimension - Strip Length inch	3-1/4 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2 in
Dimension - Thread Size	1/2
Dimension - Z (inch)	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Solid Size	1250 Kcmil
Conductor - Copper Str Size	1300 KCMIL
Conductor - Copper Str Size Range	1250 kcmil
Conductor - Material	COPPER
Conductor Size	1250 KCMIL
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	8
Minimum Pack Quantity	1
Pallet Quantity	960

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Installation Manuals - Copper Code Long Terminals Tooling and
Installation Instructions

Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - SD..031189-09
Specifications - YA454N
Video - HYDENT Compression Terminal Overview Video



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA454N-SPEC-EN | REV 10/2024