



# Compression Terminal

By Burndy  
Catalog # [YA6C2TC14E2](#)

6 AWG CU, Two Hole, 1/4 Stud Size, 3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Blue Color Code, 7 or 374 Die Index.



## Application

Wire Termination

## General

Color Code	Blue
Connector Type	LONG BARREL
Die Index	7
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810019726
UPC 12 Digit	7818100197266

## Dimensions

Dimension - B Length inch	1.12
Dimension - Bolt Hole Size inch	0.27
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	71
Dimension - Length Overall inch	2.78
Dimension - N inch	0.31
Dimension - Outside Diameter inch	0.29
Dimension - Pad Width inch	0.45
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.34 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Navy Size	30 (19) Navy
Conductor - Copper Str Navy Size Range	30 (19) Navy
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	50
Minimum Pack Quantity	1

## Product Assets

[3D Models - YA6C2TC14E2\\_MODEL-PDF](#)  
[3D Models - YA6C2TC14E2\\_MODEL-IGES](#)  
[3D Models - YA6C2TC14E2\\_MODEL-STEP](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)  
[Sales Drawings - SE..208777-01](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



**A proud member of the Hubbell Family.**