



YAEBAS4CNTNOEM, Straight Style Battery Post Terminal, 4 AWG, Negative

By Burndy

Catalog # [YAEBAS4CNTNOEM](#)

Cu Battery Post Connector Terminal, #4 AWG, Gray, 8 Index, 1-3/32 IN Strip Length, Polarity N.



Features

- Barrel is color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Supplied standard with stainless steel hardware installed
- Clamp color coded by polarity - Red is Postive, Black is Negative
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Battery Post Terminal

General

Catalog Number	YAEBAS4CNTNOEM
Color Code	Gray
Connector Type	BATTERY STRAIGHT POST
Die Index	6
Finish Type	Tin-Plated
Installation Torque	72 LBS/in
Recommended in-lb	
Material	COPPER
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562994
UPC 12 Digit	7818105629944

Dimensions

Dimension - L Length Overall	59 mm
mm	
Dimension - Length Overall	2.30 in
inch	
Physical Attribute - Tongue	Straight
Angle	

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper DLO Size	4 AWG
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M	4 AWG
Size	
Conductor - Copper Str	4 AWG
Compact Size	
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size	4 AWG
Range	
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50004535](#)
[SDS - Anti-Seize Lubricants SDS](#)
[Specifications - YAEBAS4CNTNOEM](#)