



# Compression Terminal

By Burndy  
Catalog # [YAG30L2NTCLD](#)

BURNDY; HYLUG; YAG-L-2TC-LD; For use on copper compression connection; RoHS Non Compatible; Voltage Rating: 600 - 35000 V; Color: Yellow.



## Application

Wire Termination

## General

Color Code	Yellow
Connector Type	STANDARD BARREL
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Lead Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810036235
UPC 12 Digit	7818100362355

## Dimensions

Dimension - B Length fraction	1
Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	119 mm
Dimension - Length Overall inch	4.67 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.65 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Size	250 KCMIL
Conductor - Copper Flex H Size	250 KCMIL
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	300 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	FLEX
Wire Size	250 KCMIL

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)

[Sales Drawings - SE207958](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YAG30L2NTCLD-SPEC-EN | REV 5/2024