

Compression Terminal

By Burndy
Catalog # [YAGB6CLTC38FXOEM](#)

1 Hole HYLUG™ Cu Battery Terminal, 6 AWG, 3/8" stud, 1.61" L, 0.60" W, Blue.



Application

Wire Termination

General

Catalog Number	YAGB6CLTC38FXOEM
Color Code	Blue
Connector Type	GROUNDING/STARTER LUGS
Die Index	7
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810563083
UPC 12 Digit	7818105630833

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.61 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	7/8 in
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	6 AWG
Conductor - Copper DLO Size Range	6 AWG
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex G Size Range	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE/FLEX
Wire Size	6 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Sales Drawings - 50004537](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAGB6CLTC38FXOEM-SPEC-EN | REV 6/2024