



## YAL26T38, Cu Compression, 1-Hole, 3/8" Stud, Standard Barrel, 2/0 AWG

By Burndy  
Catalog # [YAL26T38](#)



Copper HYLUG™, Single Hole w/ Inspection Window, 2/0 AWG, 3/8" Stud, 13 index, Black, Short Barrel, Electro- Tin Plated.

### Application

Wire Termination

### General

Color Code	Black
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	13
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Electro Tin plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810416990

### Dimensions

Dimension - B Length inch	0.94 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	0.83 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.19 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - CSD029213](#)



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YAL26T38-SPEC-EN | REV 5/2024