

Compression Terminal

By Burndy
Catalog # [YA26LBR](#)

Uninsulated Cu Tubing Compression Terminal, 1 Hole
W/InspWindow, 2/0 AWG Code 125 Navy Stranded Cu
Conductor, 600V - 35kV, 3/8" Stud, Standard Barrel, Bare.



Application

Wire Termination

General

Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> Chamfered Skived
Feature - Barrel Type	Standard
Finish Type	Bare
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Bright
Trade Name	HYLUG™
UPC	781810136102
UPC 12 Digit	7818101361022

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	0.83 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.19 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	38400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - sd079848-09](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YA26LBR-SPEC-EN | REV 5/2024