



## YAV2402M12, Compression Terminal

By Burndy  
Catalog # [YAV2402M12](#)

Non insulated Cu tubular terminals 2 Holes, 240mmClass2, M12 stud, Tin - Electro Plated.



### Application

Metric Wire Termination

### General

Catalog Number	YAV2402M12
Connector Type	METRIC
Die Index	20
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810442760
UPC 12 Digit	7818104427600

### Dimensions

Dimension - B Length inch	32.3 in
Dimension - Bolt Hole Size inch	0.53 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	125 mm
Dimension - Length Overall inch	4.92 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.27 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Material	COPPER
Conductor Size	240 mm <sup>2</sup>
Conductor Type	CLASS 2

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	5
Minimum Pack Quantity	5

### Product Assets

[3D Models - YAV2402M12\\_MODEL-IGES](#)  
[3D Models - YAV2402M12\\_MODEL-PDF](#)  
[3D Models - YAV2402M12\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)  
[Sales Drawings - 50025887](#)  
[Specifications - YAV2402M12](#)



A Hubbell brand