



# Uninsulated Ring Terminal For 6 AWG

By Burndy  
Catalog # [YAV6CL4](#)

Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Window, AN 5 & 6 Flex, 5/16" Stud, Short Barrel, Tin Plated.



## Application

For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance

## General

Connector Type	Ring Terminal
Die Index	39
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> <li>• DLP Copper</li> <li>• Tin Plating</li> </ul>
Military Specification	MS20659
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025628

## Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.467 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	1.43 in
Dimension - N inch	0.3 in
Dimension - Outside Diameter inch	0.30 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	5/16 in
Dimension - Z inch	0.35 in
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper Flex G Size	6
Conductor - Copper Flex H Size	6
Conductor - Copper Flex I Size	6
Conductor - Copper Flex K Size	6
Conductor - Copper Flex M Size	6
Conductor - Copper Solid Size	6
Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Size	6
Conductor - Copper Str Size Range	6
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL467</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	200
Minimum Pack Quantity	200
Pallet Quantity	99999

## Product Assets

[3D Models - YAV6CL4\\_MODEL-STEP](#)  
[3D Models - YAV6CL4\\_MODEL-PDF](#)  
[3D Models - YAV6CL4\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094161\\_F](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YAV6CL4-SPEC-EN | REV 1/2024