

YAV95FM8, Compression Terminal

By Burndy
Catalog # [YAV95FM8](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 95 mm, 8 mm Stud, 2.21 IN L, Compression, 14 Index, 27 mm Strip Length.



Application

Metric Wire Termination

General

Catalog Number	YAV95FM8
Connector Type	METRIC
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810324103
UPC 12 Digit	7818103241033

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - D inch	0.74 in
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - Inside Diameter inch	0.56 in
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.21 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	5/16
Dimension - Z (inch)	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Material	COPPER
Conductor Size	95 mm ²
Conductor Type	CLASS 5

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

[3D Models - YAV95FM8_MODEL-IGES](#)

[3D Models - YAV95FM8_MODEL-PDF](#)

[3D Models - YAV95FM8_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression](#)

[Connections](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)

[Sales Drawings - 50025612](#)

[Specifications - YAV95FM8](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV95FM8-SPEC-EN | REV 8/2024