



Uninsulated Ring Terminal For 10 - 9 AWG

By Burndy
Catalog # [YAV9CL36BOX](#)



Seamless Uninsulated Compression Heavy Duty Ring Tongue Terminal, 10-9 Str., 8-10, .97 in L, .31 in W.

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

General

Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810541586
UPC 12 Digit	7818105415866

Dimensions

Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.39 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - D inch	0.36 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.19 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.23 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	7/16 in
Dimension - Stud Size inch	#8;#10
Dimension - Z (inch)	0.15 in

Conductor Related

Conductor - Copper Str Navy Size	9 (7) Navy;9 (37) Navy;14 (7) Navy;14 (140) Navy
Conductor - Copper Str Navy Size Range	9 (7) Navy-14 (140) Navy
Conductor - Copper Str Size	10 AWG;9 AWG
Conductor - Copper Str Size Range	10 AWG - 9 AWG
Conductor Size	10 - 9 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Aircraft-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAV10L36BOX_LineArt](#)
[Sales Drawings - 50094160](#)



