

# Compression Terminal

By Burndy  
Catalog # [YAZ372N](#)

650 kcmil CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Orange Color Code, 23 Die Index.



## Application

Wire Termination

## General

Color Code	Orange
Connector Type	LONG BARREL
Die Index	23
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810227985
UPC 12 Digit	7818102279855

## Dimensions

Dimension - B Length fraction	2-13/16 in
Dimension - B Length inch	2.81 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	170 mm
Dimension - Length Overall inch	6.70 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.23 in
Dimension - Pad Width inch	1.80 in
Dimension - Strip Length inch	2-7/8
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	650 KCMIL
Conductor - Material	COPPER
Conductor Size	650 KCMIL
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)  
[Sales Drawings - se2119375](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YAZ372N-SPEC-EN | REV 8/2023