


YAE14Z3M, Nylon Flanged Fork Terminal For 16 - 14 AWG (Tape Mounted)

By Burndy
Catalog # [YAE14Z3M](#)



Nylon Flanged Fork Terminal For 16 - 14 AWG (Tape Mounted).

Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Application

Power Connector

General

Catalog Number	YAE14Z3M
Color Code	Blue
Connector Type	Flanged Fork Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Electro Tin
Temperature Rating	105° C
Trade Name	INSULUG™
UPC	781810028711
UPC 12 Digit	7818100287111

Dimensions

Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - D inch	0.02 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	1 in
Dimension - N inch	0.2 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#6 - #8
Dimension - Z (inch)	0.29 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size Range	AN16 - AN14
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	2000
Packaging Type	Reel

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section B - Small](#)

[Compression](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_YAE14Z3M_LineArt](#)

[Specifications - YAE14Z3M](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAE14Z3M-SPEC-EN | REV 8/2024