



YAGB26LTC516FXOEM, Battery Terminal, 2/0 AWG, 1-Hole, 5/16" Stud

By Burndy

Catalog # [YAGB26LTC516FXOEM](#)



Cu Battery Terminal Lug Type, 2/0 AWG, 5/16 in Stud, Connector Color Code- Orange, Die Color Code- Black, 1-Hole, 13 Die Index, Tin Plated, Terminal, Standard Barrel.

Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Wire Termination

General

Catalog Number	YAGB26LTC516FXOEM
Color Code	Black
Connector Type	GROUNDING/STARTER LUGS
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electroplated
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810547458
UPC 14 Digit GTIN	00781810547458

Dimensions

Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.06 in
Dimension - Strip Length inch	1-3/16 in

Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No
Logistics	
Minimum Pack Quantity	100

Product Assets

- Catalogs - BURNDY Master Catalog - Section C - Compression Connections
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Sales Drawings - 30008293
- Specifications - YAGB26LTC516FXOEM



A Hubbell brand