

Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAV14H](#)



Copper Compression Lug, Heavy Duty, Ring Tongue with Shroud, 1 Hole w/ Inspection Hole, 20-14 AWG, #8-#10 Stud, Short Barrel, Tin Plated.

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

General

| | |
|--------------------------------------|----------------------|
| Connector Type | Ring Terminal |
| EU RoHS Indicator | Yes |
| Feature - Barrel Style | Shrouded |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Ring |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLUG |
| Trade Name | HYLUG™ |
| Type | Ring Tongue |
| UPC | 781810024959 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 1/4 in |
| Dimension - B Length inch | 0.247 in |
| Dimension - Bolt Size fraction | #10 |
| Dimension - D inch | 0.42 in |
| Dimension - Length Overall inch | 0.95 in |
| Dimension - N inch | 0.16 in |
| Dimension - Outside Diameter inch | 0.24 in |
| Dimension - Pad Width inch | 0.31 in |
| Dimension - Stud Size inch | #10 |
| Dimension - Z (inch) | 0.24 in |

Conductor Related

| | |
|-----------------------------------|--|
| Conductor - Copper Str Size | 20 AWG;18 AWG;16 AWG;14 AWG |
| Conductor - Copper Str Size Range | 20 AWG - 14 AWG |
| Conductor Size | 16 - 14 AWG |
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size |

Certifications And Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL486 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 1000 |
| Minimum Pack Quantity | 1000 |
| Pallet Quantity | 99999 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAV14H_LineArt](#)
[Sales Drawings - 50094162](#)