



YCS30R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS30R](#)

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), Index:251.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

General

Catalog Number	YCS30R
Connector Type	Splice
Die Index	251
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810015032
UPC 14 Digit GTIN	00781810015032

Dimensions

Dimension - B Length inch	3.18 in
Dimension - L Length Overall mm	165 mm
Dimension - Length Overall inch	6.47 in
Dimension - Outside Diameter inch	1 in

Conductor Related

Conductor - AAAC 5005 Size	312.8 (19)
----------------------------	------------



Conductor - AAAC 5005 Size Range	312.8 (19) kcmil
Conductor - AAAC 6201 Size	312.8 (19)
Conductor - ACSR Str Size	266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge
Conductor - AL Str Size	266.8 kcmil

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

- [3D Models - YCS30R_MODEL-PDF](#)
- [3D Models - YCS30R_MODEL-STEP](#)
- [3D Models - YCS30R_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCS-R_LineArt](#)
- [Sales Drawings - 50115707](#)
- [Specifications - YCS30R](#)
- [Specifications - BURNDY_YCS30R_Specsheet](#)