



**YAV26LNK, Compression Terminal,
2/0 AWG, 1-Hole, 3/8" Stud,
Standard Barrel, Nickel Plated**

By Burndy
Catalog # [YAV26LNK](#)

Cu Large Size Uninsul Comp Terminal, Ring Tongue/Bvl Entry,
W/InspWindow, AN 2/0, 3/8" Stud, Seamless bbl, Nickel Plated,
44 Index.



Application

Wire Termination

General

Catalog Number	YAV26LNK
Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Nickel Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Yes
Plating Type	Nickel
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810085707
UPC 12 Digit	7818100857077

Dimensions

Dimension - B Length inch	0.782 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - Length Overall inch	2.319 in
Dimension - N inch	0.467 in
Dimension - Pad Width inch	0.934 in
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.48 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Aircraft Size	00 Aircraft
Conductor - Copper Str Aircraft Size Range	00 Aircraft
Conductor - Copper Str Size	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	23200

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094161_E](#)
[Specifications - YAV26LNK](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV26LNK-SPEC-EN | REV 8/2024