



YAV2CRSNK, Uninsulated Right Angle Ring Terminal For 2 AWG, 1-Hole, 3/8" Stud, Nickel Plated

By Burndy
Catalog # [YAV2CRSNK](#)

Uninsulated Right Angle Ring Terminal For 2 AWG (Nickel Plated).



Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

General

Catalog Number	YAV2CRSNK
Connector Type	Ring Terminal
Die Index	41
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810053164

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - G inch	1 in
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	1.27 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.47 in
Dimension - Pad Width inch	0.68 in
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	3/8 in
Dimension - Z (inch)	0.34 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 2
Conductor Size	2 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094166](#)
[Specifications - YAV2CRSNK](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV2CRSNK-SPEC-EN | REV 8/2024