



## YDS28RLY, Aluminum Single Sleeve Full Tension Splice

By Burndy  
Catalog # [YDS28RLY](#)

AL Compression Splices - Single Sleeve Full Tension,  
Accommodates: AAC, ACSR and AAAC, Die Index: 654.



## Application

For ACSR, Aluminum, 6201 And 5005 Conductors

## General

Catalog Number	YDS28RLY
Connector Type	Splice
Die Index	654
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	UNISPLICE
Trade Name	UNISPLICE™
Type	YDS-RLY
UPC	781810820766
UPC 12 Digit	7818108207666

## Dimensions

Dimension - B Length fraction	10-11/25 in
Dimension - B Length inch	10.44 in
Dimension - L Length Overall mm	533 mm
Dimension - Length Overall inch	21 in
Dimension - Outside Diameter inch	1.02 in

## Conductor Related

Conductor - AAAC 5005 Size	246.9 (7) kcmil
Conductor - AAAC 5005 Size Range	246.9 (7) kcmil
Conductor - AAAC 6201 Size	246.9 (7) kcmil
Conductor - AAAC 6201 Size Range	246.9 (7) kcmil
Conductor - ACSR Cmpst Size	4/0 AWG
Conductor - ACSR Cmpst Size Range	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	1800

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YDS-RLY\\_LineArt](#)  
[Sales Drawings - SD..053576-01](#)  
[Specifications - YDS28RLY](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YDS28RLY-SPEC-EN | REV 8/2024