

# YDS4CA, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy  
Catalog # [YDS4CA](#)



Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension), Die Index: 162, 2-5/8 L.

### Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

### Application

For All Aluminum Compressed And Compact Conductors

### General

Catalog Number	YDS4CA
Color Code	Orange
Connector Type	Splice
Die Index	162
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-A
UPC	781810015377
UPC 14 Digit GTIN	00781810015377

### Dimensions

Dimension - B Length inch	1.25 in
Dimension - Inside Diameter inch	0.24 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Outside Diameter inch	0.4 in

### Conductor Related

Conductor - AAAC 5005 Size	48.69 (7) kcmil
Conductor - AAAC 5005 Size Range	48.69 (7) kcmil
Conductor - AAAC 6201 Size	48.69 (7) kcmil
Conductor - AAAC 6201 Size Range	48.69 (7) kcmil
Conductor - ACAR Str Size	4 (7) AWG
Conductor - ACAR Str Size Range	4 (7) AWG
Conductor - ACSR Cmpt Size	4 AWG
Conductor - ACSR Cmpt Size Range	4 AWG
Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	29600

### Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YDS-A\\_LineArt](#)  
[Sales Drawings - SC019521-01](#)  
[Specifications - YDS4CA](#)