



YAV50M14, Compression Terminal

By Burndy

Catalog # [YAV50M14](#)

Copper Tubing Terminal; 1 Hole W/insp window; 50 mm Class 2; 12 Index; 14 mm Stud.



Application

Metric Wire Termination

General

Catalog Number	YAV50M14
Connector Type	METRIC
Die Index	12
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323755
UPC 12 Digit	7818103237555

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.63 in
Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	1.12 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	0.36 in
Dimension - L Length Overall mm	3 mm
Dimension - Length Overall inch	0.12 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	0.67 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	#14
Dimension - Z (inch)	0.57 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	COPPER
Conductor Size	50 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	48000

Product Assets

[3D Models - YAV50M14_MODEL-IGES](#)
[3D Models - YAV50M14_MODEL-PDF](#)
[3D Models - YAV50M14_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025521](#)
[Specifications - YAV50M14](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV50M14-SPEC-EN | REV 8/2024