



YE25LH97, Compression Terminal Plug, Oil/Water Tight with Shroud, Tin-Plated, 1/0 Str

By Burndy
Catalog # [YE25LH97](#)

Oil and water-tight terminal with shrouded, tin-plated, CU barrel and brazed plug Used for terminating insulated CU conductor at cutout or transformer, 11.38 IN L.

Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

Application

Wire Termination

General

Catalog Number	YE25LH97
Connector Type	INLINE PIN
Die Index	163
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Finish Type	Tin-Plated
Insulation	Y
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYSEALPLUG
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810023365
UPC 14 Digit GTIN	00781810023365

Dimensions

Dimension - B Length fraction	2-5/8 in
Dimension - B Length inch	2.62 in
Dimension - Inside Diameter inch	0.98 in
Dimension - L Length Overall mm	283 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	11.13 in
Dimension - P inch	8.06 in



Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str	1/0 AWG
Compact Size	
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	4200

Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YE27LH94_LineArt](#)
[Sales Drawings - SA055640-01](#)
[Specifications - YE25LH97](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YE25LH97-SPEC-EN | REV 3/2025