



YE27LH94, Compression Terminal Plug, Oil/Water Tight with Shroud, 3/0 Str

By Burndy
Catalog # [YE27LH94](#)



Oil and water-tight terminal with shrouded, tin-plated, copper barrel and brazed plug.

Application

Wire Termination

General

Catalog Number	YE27LH94
Connector Type	INLINE PIN
Die Index	243
Feature - Barrel Style	Shrouded
Finish Type	Tin-Plated
Insulation	Y
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810104613
UPC 12 Digit	7818101046133

Dimensions

Dimension - B Length fraction	1-5/16 in
Dimension - B Length inch	1.34 in
Dimension - L Length Overall mm	180 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	7.09 in
Dimension - P inch	4.00 in
Dimension - Width inch	0.80 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Str Compact Size	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	4900

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_YE27LH94_LineArt](#)

[Sales Drawings - SD068061-01](#)

[Specifications - YE27LH94](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YE27LH94-SPEC-EN | REV 8/2024