



YAV95M14, Compression Terminal

By Burndy

Catalog # [YAV95M14](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 95 mm, 14 mm Stud, 2.40 IN L, Compression, 14 Index, 22 mm Strip Length.



Application

Metric Wire Termination

General

Catalog Number	YAV95M14
Connector Type	METRIC
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none">ChamferedSkived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810324127
UPC 12 Digit	7818103241277

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	61
Dimension - Length Overall inch	2.4
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.63
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	0.87 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.57 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size Range	95 mm ² , 2/0 AWG
Conductor - Material	COPPER
Conductor Size	95 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

[3D Models - YAV95M14_MODEL-PDF](#)
[3D Models - YAV95M14_MODEL-STEP](#)
[3D Models - YAV95M14_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025521](#)
[Specifications - YAV95M14](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV95M14-SPEC-EN | REV 8/2024