



**YGA292N Compression Grounding
Lug, 250 kcmil Cu, 2-Hole, 1/2"
Stud, 1-3/4" Spacing**

By Burndy
Catalog # [YGA292N](#)

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole;
1/2" Stud; 1-3/4" Spacing; Long Barrel; Accommodates: 250
kcmil; 5.16" Length



Application

For Grounding Applications And Direct Burial In Earth Or Concrete

General

Catalog Number	YGA292N
Color Code	Yellow
Connector Type	Terminal
Die Index	16
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminals
UPC	781810220337
UPC 12 Digit	7818102203377

Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.21 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.09 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Width fraction	1/2 in
Dimension - Width inch	0.53 in

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL 467,486A• CSA Certified• Direct Burial
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	4640

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YGA2N_LineArt](#)
[Sales Drawings - SD..082469-01](#)
[Specifications - YGA292N](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YGA292N-SPEC-EN | REV 8/2024