

YGHR26C12TN Figure 8 Compression Ground Rod Connector

By Burndy

Catalog # [YGHR26C12TN](#)



HYTAIL™ Ground Rod Figure 8 Compression Tap Connector.

Features

- High torque strength ground rod connector accepts a wide range of copper conductors to ground rod
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

General

Catalog Number	YGHR26C12TN
Connector Type	Tap
Die Index	998;1012
Material	Copper
Physical Attribute - Number of	1
Crimps Required	
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYTAIL™
Type	Taps
UPC	621945150591
UPC 14 Digit GTIN	00621945150591

Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	1/2
Dimension - Height fraction	1-47/50 in
Dimension - Height inch	1.94 in
Dimension - Height mm	49.3 mm
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
-----------------------------	--------------------------

Conductor - Copper Str Size Range	2 AWG - 2/0 AWG
Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size A• Rod-Size B

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL467• IEEE 837
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	20
Minimum Pack Quantity	12
Pallet Quantity	4640

Product Assets

[3D Models - YGHR26C12TN_MODEL-PDF](#)
[3D Models - YGHR26C12TN_MODEL-STEP](#)
[3D Models - YGHR26C12TN_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd..088266-01](#)
[Specifications - YGHR26C12TN](#)