

Compression H-Tap

By Burndy
Catalog # [YH3931WCC](#)



Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 750 KCMIL-350 KCMIL Class B,C, 535 KCMIL DLO, 550 KCMIL-450 KCMIL Class I, Tap 1: 4/0 AWG-1/0 AWG Class B,C, 250 KCMIL-1/0 AWG Class I, DLO, 4/0 AWG Class K, Tap 2: 1 AWG-6 AWG Solid, 1 AWG-6 AWG Class B,C, 1 AWG-8 AWG Class I, DLO, with clear cover. See sale drawing for metric wire size accommodates

Application

Wire Tap

General

Color Code	Yellow
Connector Type	H-TAP W/CLR COVER
Die Index	KR
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810436486
UPC 12 Digit	7818104364866

Dimensions

Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	1-1/16
Dimension - Width inch	2.97 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	500
Conductor - Copper Flex G Tap	1/0;2/0;3/0;4/0;250
Conductor - Copper Flex H Tap	1/0;2/0;3/0;4/0;250
Conductor - Copper Flex I Run	550 KCMIL-500 KCMIL
Conductor - Copper Flex I Tap	1/0;2/0;3/0;4/0;250
Conductor - Copper Flex I Tap Range	250 KCMIL-1/0 AWG
Conductor - Copper Flex K Run	500
Conductor - Copper Flex K Tap	1/0;2/0;3/0;4/0;250
Conductor - Copper Flex K Tap Range	4/0 AWG
Conductor - Copper Flex M Run	500
Conductor - Copper Flex M Tap	1/0;2/0;3/0;4/0;250
Conductor - Copper Str Run	350;400;450;500;550;600;700
Conductor - Copper Str Run Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Tap	1/0;2/0;3/0;4/0
Conductor - Copper Str Tap Range	4/0 AWG-1/0 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

Product Assets

[Catalogs](#) [Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YH3931WCC-SPEC-EN | REV 8/2023