


# Compression H-Tap

By Burndy  
Catalog # [YH4429WCC](#)



Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 1000 KCMIL-750 KCMIL Class B,C, 777 KCMIL-535 KCMIL DLO, 750-500 KCMIL Class I, Tap 1: 250 KCMIL-2 AWG Class B,C, 4/0 AWG-2 AWG Class I, DLO, kitted with clear cover. See sale drawing for metric wire size accommodates

## Application

Wire Tap

## General

Color Code	Yellow
Connector Type	H-TAP W/CLR COVER
Die Index	KR
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810436509
UPC 12 Digit	7818104365099

## Dimensions

Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Strip Length inch	1-3/8
Dimension - Width inch	3.32 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Run	500;600;700
Conductor - Copper Flex G Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex H Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex I Run	750 KCMIL-500 KCMIL
Conductor - Copper Flex I Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex I Tap Range	4/0 AWG-2 AWG
Conductor - Copper Flex K Run	500;600;700
Conductor - Copper Flex K Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex M Run	500;600;700
Conductor - Copper Flex M Tap	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Run	700;750;800;850;900;1000
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Tap	2;1;1/0;2/0;3/0;4/0;250
Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD\\_206566-01](#)



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YH4429WCC-SPEC-EN | REV 8/2023