



# Compression C-Tap

By Burndy  
Catalog # [YC26L12TN](#)

Cu Thin Wall C-Tap, Compression, 2/0 - #1 AWG(Main), #1 - #12 AWG(Tap), 600 V, Tin Plated.



## Application

Wire Tap

## General

|                    |                      |
|--------------------|----------------------|
| Color Code         | Purple               |
| Connector Type     | C-TAP                |
| Die Index          | 15                   |
| Finish Type        | Tin-Plated           |
| Material           | COPPER               |
| Plated             | Y                    |
| Plating Type       | Tin - Electro Plated |
| Temperature Rating | 194                  |
| Trade Name         | CRIMPIT™             |
| Type               | YC-L Series          |
| UPC                | 781810040256         |
| UPC 12 Digit       | 7818100402566        |

## Dimensions

|                               |          |
|-------------------------------|----------|
| Dimension - B Length fraction | 11/16 in |
| Dimension - B Length inch     | 0.69 in  |
| Dimension - D inch            | 1.75 in  |
| Dimension - Pad Width inch    | 0.43 in  |
| Dimension - Strip Length inch | 1-13/16  |

## Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 35000 |
|-------------------|-------|

## Conductor Related

|                                  |                |
|----------------------------------|----------------|
| Conductor - Copper Str Run       | 2/0 AWG-1 AWG  |
| Conductor - Copper Str Run Range | 2/0 AWG-1 AWG  |
| Conductor - Copper Str Tap       | 1 AWG-12 AWG   |
| Conductor - Copper Str Tap Range | 1 AWG-12 AWG   |
| Conductor - Material             | COPPER         |
| Conductor Size                   | 2/0 AWG-12 AWG |
| Conductor Type                   | CODE           |

## Certifications And Compliance

|                                    |              |
|------------------------------------|--------------|
| Certification - CSA Approved       | Yes          |
| Certification - ETL                | No           |
| Certification - UL Recognized      | No           |
| Certification - cULus              | No           |
| Industry Standard(s)               | UL 486A-486B |
| Standards - RoHS Compliance Status | CM           |
| UL Listed                          | Yes          |

## Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 150   |
| Minimum Pack Quantity | 150   |
| Pallet Quantity       | 27000 |

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SC..208529-01](#)



A proud member of the Hubbell Family.