



YC28A26, Aluminum C-Shape Connector

By Burndy
Catalog # [YC28A26](#)



Range-taking, C-shaped AL compression tap, Run: Aluminum: 3/0- 4/0, ACSR: 3/0-4/0, Tap: Aluminum: 2/0- 2/0, ACSR: 2/0- 2/0.

General

Die Index	H
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810125724
UPC 12 Digit	7818101257244

Dimensions

Dimension - Height inch	1.61 in
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in

Conductor Related

Conductor - AAAC 5005 Run	195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 5005 Run Range	195.7 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 5005 Tap	155.4 (7) kcmil
Conductor - AAAC 5005 Tap Range	155.4 (7) kcmil
Conductor - AAAC 6201 Run	195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 6201 Run Range	195.7 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Tap	155.4 (7) kcmil
Conductor - AAAC 6201 Tap Range	155.4 (7) kcmil
Conductor - ACSR Cmptr Run	3/0 AWG;4/0 AWG
Conductor - ACSR Cmptr Run Range	3/0 AWG-4/0 AWG
Conductor - ACSR Cmptr Tap	2/0 AWG
Conductor - ACSR Cmptr Tap Range	2/0 AWG
Conductor - ACSR Str Run	3/0 AWG - 4/0 AWG
Conductor - ACSR Str Tap	2 Str
Conductor - AL Str Run	3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	3/0 AWG - 4/0 AWG
Conductor - AL Str Tap	2/0 Str
Conductor - AL Str Tap Range	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	6000

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_ycala](#)
- [Sales Drawings - 27166](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YC28A26-SPEC-EN | REV 5/2024