


YP27AU4, Figure 3-shaped Aluminum Connector with adjustable spacer

By Burndy
Catalog # [YP27AU4](#)



Wide range, universal and reversible, Figure 3 shaped aluminum connector with adjustable overhanging spacer that separates conductors.

Application

For Copper, Aluminum Or ACSR Conductors

General

Catalog Number	YP27AU4
Die Index	D3
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	CABELOK CRIMPIT
Trade Name	CABELOK™ CRIMPIT™
Type	YP-U
UPC	781810134481
UPC 12 Digit	7818101344811

Dimensions

Dimension - Height inch	1.70 in
Dimension - Length Overall inch	1.69 in
Dimension - Width inch	0.97 in

Conductor Related

Conductor - ACSR Str Size A	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG
Conductor - ACSR Str Size A Range	1/0 (6/1) Raven AWG-2/0 (6/1) Quail AWG
Conductor - ACSR Str Size B	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size A	1/0 AWG;2/0 AWG
Conductor - AL Str Size A Range	1/0 AWG-2/0 AWG
Conductor - AL Str Size B	6 AWG;4 AWG
Conductor - AL Str Size B Range	6 AWG-4 AWG
Conductor - Copper Solid Size A	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size A Range	2/0 AWG-4/0 AWG
Conductor - Copper Solid Size B	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size B Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size A	1/0 ;2/0 AWG;3/0 AWG
Conductor - Copper Str Size A Range	1/0 -3/0 AWG
Conductor - Copper Str Size B	6 AWG;5 AWG;4 AWG;3 AWG
Conductor - Copper Str Size B Range	6 AWG-3 AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YPU_Lineart](#)
[Sales Drawings - sd045569-01](#)
[Specifications - YP27AU4](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YP27AU4-SPEC-EN | REV 8/2024