

## YCA2R2N, Al compression lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing, #2

By Burndy  
Catalog # [YCA2R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 5.90 IN L

### Features

- Aluminum Compression HYLUG, 2-hole NEMA 1/2" Stud, 1-3/4" Spacing

### Application

For ACSR/6201/5005 (Compressed/Compact), Aluminum

### General

Catalog Number	YCA2R2N
Connector Type	Terminal
Construction Material - Main	Aluminum
Die Index	239
EU RoHS Indicator	Yes
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	Terminals, TERMINAL
Type	YCA-R-N, Terminal
UPC	781810016633
UPC 14 Digit GTIN	00781810016633

### Dimensions

Dimension - B Length inch	1.61 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.90 in



Dimension - Outside Diameter inch	0.52 in
Dimension - Pad Width inch	1.25 in

### Conductor Related

Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	25
-----------------------	----

### Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YCA\\_LineArt](#)  
[Sales Drawings - SD..029515-01](#)  
[Specifications - YCA2R2N](#)