

YCA2R2N, Al compression terminal 2-Hole, 1/2" Stud, 1-3/4" Spacing, #2 AWG, ACSR, AAC, AAAC

By Burndy

Catalog # [YCA2RL2N](#)



Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus, Die index: BG, 243, 687.

General

Catalog Number	YCA2RL2N
Connector Type	Terminal
Die Index	243;687;BG
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810408
UPC 12 Digit	7818108104088

Dimensions

Dimension - B Length inch	2.20 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6 in
Dimension - Outside Diameter inch	0.66 in
Dimension - Pad Width inch	0.91 in

Conductor Related

Conductor - ACSR Cmppt Size Range	2 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AAC

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	12000

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCA_LineArt](#)
- [Sales Drawings - SD052276-01](#)
- [Specifications - YCA2RL2N](#)



A Hubbell brand