

## YCA37R2N, Al Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy

Catalog # [YCA37R2N](#)



AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 8.15 IN L.

### Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

### General

Catalog Number	YCA37R2N
Connector Type	Terminal
Die Index	261
EU RoHS Indicator	Yes
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Trade Name	HYLUG™
Type	YCA-R-N
UPC	781810810705
UPC 12 Digit	7818108107055

### Dimensions

Dimension - B Length inch	3.65 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	207 mm
Dimension - Length Overall inch	8.15 in
Dimension - Pad Width inch	1.94 in

### Conductor Related

Conductor - ACSR Str Size	477 (24-7) kcmil; 477 (26-7) kcmil; 477 (30-7) kcmil, 556.5 (18-1)
Conductor - ACSR Str Size Range	477 (24-7) kcmil; 477 (26-7) kcmil; 477 (30-7) kcmil, 556.5 (18-1)
Conductor - AL Str Size	556 kcmil
Conductor - AL Str Size Range	556 kcmil

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	2880

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YCA\\_LineArt](#)
- [Sales Drawings - SD..029515-01](#)
- [Specifications - YCA37R2N](#)