



# YCAK35R4N

By Burndy  
Catalog # [YCAK35R4N](#)



AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 7.34 IN L.

## Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

## General

|                                        |                      |
|----------------------------------------|----------------------|
| Die Index                              | 317                  |
| EU RoHS Indicator                      | Yes                  |
| Material                               | Aluminum             |
| Physical Attribute - Pad Configuration | 4 Hole NEMA          |
| Plated                                 | N                    |
| Plating Type                           | Unplated             |
| Prefilled Oxide Inhibitor              | Y                    |
| Sub Brand                              | COMPRESSION TERMINAL |
| Type                                   | YCAK-R-N             |
| UPC                                    | 781810016756         |
| UPC 12 Digit                           | 7818100167566        |

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length inch       | 3.05 in |
| Dimension - Bolt Hole Size inch | 0.5 in  |
| Dimension - Hole Size inch      | 0.56 in |
| Dimension - L Length Overall mm | 187 mm  |
| Dimension - Length Overall inch | 7.34 in |
| Dimension - Pad Width inch      | 3 in    |

## Conductor Related

|                                 |                                                     |
|---------------------------------|-----------------------------------------------------|
| Conductor - ACSR Str Size       | 397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil |
| Conductor - ACSR Str Size Range | 397.5 kcmil (26-7,18-1,30-7 STR)                    |
| Conductor - AL Str Size         | 397 kcmil                                           |
| Conductor - AL Str Size Range   | 397 kcmil                                           |

## Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

- [3D Models - YCAK35R4N\\_MODEL-STEP](#)
- [3D Models - YCAK35R4N\\_MODEL-PDF](#)
- [3D Models - YCAK35R4N\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..029515-01](#)



A proud member of the Hubbell Family.