



# YCR25RG6

By Burndy  
Catalog # YCR25RG6



Aluminum Reducer, Designed for joining (i) Cu to Alum. or ACSR (ii) Alum or ACSR to Alum. or ACSR, Barrels Partially filled with PENETROX™ and Sealed.

### General

Connector Type	Reducer
Die Index	654;705
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYREDUCER™
UPC	781810109014
UPC 12 Digit	7818101090144

### Dimensions

Dimension - B Length fraction	2-7/8 in
Dimension - B Length inch	2.88 in
Dimension - L Length Overall mm	162 mm
Dimension - Length Overall inch	6.38 in
Dimension - Outside Diameter inch	1.06 in

### Conductor Related

Conductor - ACSR Str Size A	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size A Range	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size A Range	1/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - AL Str Size B Range	1/0 AWG
Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size A Range	1/0 AWG
Conductor - Copper Str Size B	1/0 AWG
Conductor - Copper Str Size B Range	1/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size A</li> <li>• AL C Str-Size A</li> <li>• CU C Str-Size A</li> <li>• ACSR C Str-Size B</li> <li>• AL C Str-Size B</li> <li>• CU C Str-Size B</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	4440

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD057607-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YCR25RG6-SPEC-EN | REV 8/2023